

**NB100-77666R****CD105 Antibody (MJ7/18) [DyLight 550]****Unit Size**

0.1 mg

**Concentration**

0.5 mg/ml

**Storage**

Store at 4C in the dark.

**Applications**

WB, FLOW, IHC, IHC-Fr, IP

**Species**

Mouse

**Host**

Rat

**Clonality**

Monoclonal

**Isotype**

IgG2a Kappa

**Conjugate**

DyLight 550

**Purity**

Immunogen affinity purified

**Preservative**

No Preservative

**Marker**

Hematopoietic Stem Cell Marker

**Specificity/Sensitivity**

CD105 (MJ7/18)

**Immunogen**

inflamed mouse skin

**Recommended Dilutions**

Flow Cytometry, Immunoprecipitation, Western Blot, Immunohistochemistry-Frozen, Immunohistochemistry

**Buffer**

50mM sodium borate

**Uses**

Each lot of this antibody is quality control tested by immunofluorescent staining with flow cytometric analysis. For immunofluorescent staining, the suggested use of this reagent is: 0.5 microgram per one million cells in 100 microliter volume. Immunohistochemistry-frozen section. It is recommended that the reagent be titrated for optimal performance for each application.

**Images**

This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: [www.novusbio.com/NB100-77666R](http://www.novusbio.com/NB100-77666R)

Updated 3/9/2013 2.0

**Limitations:** This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit [www.novusbio.com/guarantee](http://www.novusbio.com/guarantee).**

**Novus USA**

8100 Southpark Way, A-8  
 Littleton, CO 80120  
 p) 888-506-6887  
 p) 303-730-1950  
 f) 303-730-1966  
[novus@novusbio.com](mailto:novus@novusbio.com)

**Novus Canada**

461 North Service Road West,  
 Unit B37  
 Oakville, ON L6M 2V5  
 p) 855-668-8722  
 f) 905-827-6402  
[canada@novusbio.com](mailto:canada@novusbio.com)

**Novus Europe**

12 Cambridge Science Park  
 Cambridge, UK CB4 0FQ  
 UK: p) +44-1223-426-001, f) +44-871-971-1635  
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79  
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340  
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31  
[europe@novusbio.com](mailto:europe@novusbio.com)

