

NB100-64752**Respiratory Syncytial Virus Nucleoprotein Antibody (RSV3132 (B023))****Unit Size**

0.5 mg

Concentration

1.0 mg/ml

Storage

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications

ELISA, ICC/IF, IHC, IHC-Fr

Species

Virus

Host

Mouse

Clonality

Monoclonal

Isotype

IgG1

Purity

IgG purified

Preservative

0.09% Sodium Azide

Specificity/Sensitivity

Recognizes an epitope within the 42kD RSV nucleoprotein.

Immunogen

Bovine RSV strains: 127, SNK and 9007. Human RSV strains: A2, Long, Randall and 8/60.

Recommended Dilutions

ELISA

Immunocytochemistry/Immunofluorescence

Immunohistochemistry

Immunohistochemistry-Frozen 1:100

Buffer

Phosphate buffered saline pH7.5

Uses

Suitable for use as detection reagent with NB100-64495 as capture reagent in sandwich ELISA.

ImagesThis product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB100-64752

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

