

**NB100-62936****Streptococcus streptokinase Antibody****Unit Size**

0.5 ml

**Concentration**

5.0 mg/ml

**Storage**

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

**Applications**

ELISA

**Species**

Non-species specific

**Host**

Rabbit

**Clonality**

Polyclonal

**Purity**

Protein G purified

**Preservative**

0.09% Sodium Azide

**Specificity/Sensitivity**

This product is specific for Streptococcus streptokinase, a metallo-enzyme produced by various strains of Streptococcus. It is 415 amino acids in length with a MW of approximately 47kDa. Streptokinase can be used as an anti thrombotic because it can liquify blood clots by converting plasminogen to plasmin.

**Immunogen**

Streptococcus streptokinase bacterial protein prepared from Lancefield strain of Streptococcus-beta hemolyticus.

**Recommended Dilutions**

ELISA 1/20-1/200

**Buffer**

PBS

**Uses**

This antibody is useful for ELISA

**Images**

This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: [www.novusbio.com/NB100-62936](http://www.novusbio.com/NB100-62936)

Updated 3/9/2013 2.0

**Limitations:** This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit [www.novusbio.com/guarantee](http://www.novusbio.com/guarantee).**

**Novus USA**

8100 Southpark Way, A-8  
 Littleton, CO 80120  
 p) 888-506-6887  
 p) 303-730-1950  
 f) 303-730-1966  
[novus@novusbio.com](mailto:novus@novusbio.com)

**Novus Canada**

461 North Service Road West,  
 Unit B37  
 Oakville, ON L6M 2V5  
 p) 855-668-8722  
 f) 905-827-6402  
[canada@novusbio.com](mailto:canada@novusbio.com)

**Novus Europe**

12 Cambridge Science Park  
 Cambridge, UK CB4 0FQ  
 UK: p) +44-1223-426-001, f) +44-871-971-1635  
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79  
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340  
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31  
[europe@novusbio.com](mailto:europe@novusbio.com)

