

NB100-56397**Ube2V1 Antibody****Unit Size**

0.1 mg

Concentration

0.5 mg/ml

Storage

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications

WB

Species

Human

Host

Rabbit

Clonality

Polyclonal

Purity

Protein G purified

Preservative

0.05% Sodium Azide

Specificity/Sensitivity

A protein band of approximate molecular weight of 20 kD can be seen in Jurkat, RAW and HeLa cell lysates. This may also recognize isoform b of UBE2V1.

Immunogen

A synthetic peptide corresponding to amino acids 31-49 of human UBE2V1a. Genbank accession no. NP_954595.1.

Recommended Dilutions

Western Blot 1-3 ug/ml

Buffer


PBS containing 0.2% gelatin

Uses

Western Blot

Images

Western Blot: UBE2V1a Antibody [NB100-56397] -
 Western blot analysis of UBE2V1a in Jurkat cell
 lysate using NB100-56397 at 1 ug/ml.



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

