

NB100-56492**DUSP13 Antibody****Unit Size**

0.1 mg

Concentration

Please see the vial label for concentration.

Storage

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications

WB

Species

Human, Primate

Host

Rabbit

Clonality

Polyclonal

Purity

Protein G purified

Preservative

0.05% Sodium Azide

Specificity/Sensitivity

The amino acid sequence used as immunogen has 100% identity in human, and chimp, 93% identity in rhesus monkey and 86% identity in bovine. This will detect isoform 3 of human DUSP13. It will not detect isoforms 1 or 2.

Immunogen

A portion of amino acids 50-100 of human DUSP13 was used as the immunogen.

Recommended Dilutions

Western Blot 0.5-2 ug/ml

Buffer

PBS containing 0.2% gelatin

Uses

Western Blot

Images

Western Blot: DUSP13 (isoform 3) Antibody [NB100-56492] - Western blot analysis of DUSP13 in human skeletal muscle lysate in the 1) absence and 2) presence of immunizing peptide using NB100-56492 at 0.5 ug/ml.



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

