

**NB100-2381R****VEGFA Antibody [DyLight 550]****Unit Size**

0.1 ml

**Concentration**

1.1 mg/ml

**Storage**

Store at 4°C in the dark.

**Applications**

WB

**Species**

Human, Mouse, Rat, Bovine, Canine, Chicken, Guinea Pig, Porcine

**Host**

Rabbit

**Clonality**

Polyclonal

**Conjugate**

DyLight 550

**Purity**

Affinity purified

**Preservative**

No Preservative

**Specificity/Sensitivity**

This is specific for VEGFA.

**Immunogen**

A synthetic peptide made to an internal region of the human VEGFA protein sequence (between residues 150-250). [Swiss-Prot# P15692]

**Recommended Dilutions**

Western Blot - 1 ug/ml (ECL)

**Buffer**

50mM sodium borate

**Uses**

This antibody is useful for Western blot analysis, where a band is seen at ~42 kDa with a chimera transfected lysate, representing the homodimer VEGFA. Another faint band is seen at ~21 kDa, representing the monodimer form of VEGFA.

**Images**This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: [www.novusbio.com/NB100-2381R](http://www.novusbio.com/NB100-2381R)

Updated 3/9/2013 2.0

**Limitations:** This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit [www.novusbio.com/guarantee](http://www.novusbio.com/guarantee).**

**Novus USA**

8100 Southpark Way, A-8  
 Littleton, CO 80120  
 p) 888-506-6887  
 p) 303-730-1950  
 f) 303-730-1966  
[novus@novusbio.com](mailto:novus@novusbio.com)

**Novus Canada**

461 North Service Road West,  
 Unit B37  
 Oakville, ON L6M 2V5  
 p) 855-668-8722  
 f) 905-827-6402  
[canada@novusbio.com](mailto:canada@novusbio.com)

**Novus Europe**

12 Cambridge Science Park  
 Cambridge, UK CB4 0FQ  
 UK: p) +44-1223-426-001, f) +44-871-971-1635  
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79  
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340  
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31  
[europe@novusbio.com](mailto:europe@novusbio.com)

