

NB100-2522H**SIRT6 Antibody [HRP]****Unit Size**

0.1 ml

Concentration

1.12 mg/ml

Storage

Store at 4°C in the dark.

Applications

WB

Species

Mouse

Host

Rabbit

Clonality

Polyclonal

Conjugate

HRP

Purity

Affinity purified

Preservative

No Preservative

Specificity/Sensitivity

SIRT6

Immunogen

A synthetic peptide made to a C-terminal region of the mouse SIRT6 protein (within residues 250-334). [Swiss-Prot P59941]

Recommended Dilutions

Western Blot 0.5-2.0 ug/ml

Buffer

PBS

Uses

This antibody is useful for Western blot analysis, where a band is seen at ~37 kDa. A non-specific higher MW band can be seen at ~61 kDa, of equal or greater intensity than the mSIRT6 band.

ImagesThis product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB100-2522H

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. For more information on our guarantee, please visit www.novusbio.com/guarantee.

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

