

NB100-530H**VEGF Receptor 2 Antibody [HRP]****Unit Size**

0.1 ml

Concentration

2.55 mg/ml

Storage

Store at 4C in the dark.

Applications

WB

Species

Human

Host

Rabbit

Clonality

Polyclonal

Conjugate

HRP

Purity

Affinity purified

Preservative

No Preservative

Marker

Hemangioblast Marker, Stem Cell Marker

Specificity/Sensitivity

This is specific for VEGFR-2.

Immunogen

A synthetic peptide made to a C-terminal region of the murine VEGFR2 protein sequence (between residues 1300-1367).

Recommended Dilutions

Western Blot 1:250-1:1000

Buffer

PBS

Uses

This antibody is useful for Western blot analysis, where a doublet is seen at ~150 kDa. Optimal working dilutions should be determined by the investigator.

ImagesThis product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB100-530H

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

