

Datasheet

APOA2 polyclonal antibody (A01)

Catalog Number: H00000336-A01

Regulation Status: For research use only (RUO)

Product Description: Mouse polyclonal antibody raised against a full-length recombinant APOA2.

Immunogen: APOA2 (AAH05282, 1 a.a. ~ 100 a.a)
full-length recombinant protein with GST tag.

Sequence:

MKLLAATVLLLTICSLEGALVRRQAKEPCVESLVSQYF
QTVTDYDGKDLMEKVKSPQLQAEAKSYFEKSKEQLTPLI
KKAGTELNVNLSYFVELGTQPATQ

Host: Mouse

Reactivity: Human

Applications: ELISA, WB-Re

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Storage Buffer: 50 % glycerol

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 336

Gene Symbol: APOA2

Gene Alias: -

Gene Summary: This gene encodes apolipoprotein (apo-) A-II, which is the second most abundant protein of the high density lipoprotein particles. The protein is found in plasma as a monomer, homodimer, or heterodimer with apolipoprotein D. Defects in this gene may result in apolipoprotein A-II deficiency or hypercholesterolemia. [provided by RefSeq]