

## Datasheet

### ***Streptococcus* Group A monoclonal antibody, clone 501**

**Catalog Number:** MAB4342

**Regulation Status:** For research use only (RUO)

**Product Description:** Mouse monoclonal antibody raised against *Streptococcus* Group A.

**Clone Name:** 501

**Immunogen:** Native *Streptococcus agalactiae*.

**Host:** Mouse

**Reactivity:** *Streptococcus*

**Applications:** ELISA

(See our web site product page for detailed applications information)

**Protocols:** See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

**Specificity:** Recognizes *Streptococcus* Group A. Does not cross react with *Streptococcus* groups B-G, *Streptococcus pneumonia*, *Staphylococcus aureus*, *Corynebacterium diphtheriae*, *Streptococcus salivarius* or *Micrococcus mucilagines*.

**Form:** Liquid

**Isotype:** IgG2a

**Recommend Usage:** The optimal working dilution should be determined by the end user.

**Storage Buffer:** In buffer containing 0.1% sodium azide

**Storage Instruction:** Store at -20°C. For long term storage store at -80°C.

Aliquot to avoid repeated freezing and thawing.