

## Datasheet

### PRV1 polyclonal antibody (A01)

**Catalog Number:** H00057126-A01

**Regulation Status:** For research use only (RUO)

**Product Description:** Mouse polyclonal antibody raised against a partial recombinant PRV1.

**Immunogen:** PRV1 (AAH29167, 21 a.a. ~ 120 a.a)  
partial recombinant protein with GST tag.

**Sequence:**

ALLCQFGTVQHVKVSDLPRQWTPKNTSCDSGLGCQ  
DTLMLIESGPQVSLVLSKGCTEAKDQEPRVTEHRMGP  
GLSLISYTFVCRQEDFCNNLVNSLPLW

**Host:** Mouse

**Reactivity:** Human

**Applications:** ELISA, WB-Re

(See our web site product page for detailed applications information)

**Protocols:** See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

**Storage Buffer:** 50 % glycerol

**Storage Instruction:** Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

**Entrez GeneID:** 57126

**Gene Symbol:** CD177

**Gene Alias:** HNA2A, NB1, PRV1

**Gene Summary:** NB1, a glycosyl-phosphatidylinositol (GPI)-linked N-glycosylated cell surface glycoprotein, was first described in a case of neonatal alloimmune neutropenia (Lalezari et al., 1971 [PubMed 5552408]).[supplied by OMIM]