

Datasheet

Apoa1 polyclonal antibody

Catalog Number: PAB13883

Regulation Status: For research use only (RUO)

Product Description: Rabbit polyclonal antibody raised against native ApoA1.

Immunogen: Native purified ApoA1 from mouse plasma high density lipoprotein.

Host: Rabbit

Reactivity: Human, Mouse

Applications: ID, RIA, WB

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Specificity: Extremely low recognition of human Apo A1.

Form: Liquid

Recommend Usage: The optimal working dilution should be determined by the end user.

Storage Buffer: In buffer containing 0.025% sodium azide

Storage Instruction: Store at -80°C.
Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 11806

Gene Symbol: ApoA1

Gene Alias: Alp-1, ApoA-1, Brp-14, Ltw-1, Lvtw-1, MGC102525, Sep-1, Sep-2, Sep2