

## Datasheet

### GPR15 polyclonal antibody

**Catalog Number:** PAB16214

**Regulation Status:** For research use only (RUO)

**Product Description:** Rabbit polyclonal antibody raised against synthetic peptide of GPR15.

**Immunogen:** A synthetic peptide (conjugated with KLH) corresponding to human GPR15.

**Host:** Rabbit

**Reactivity:** Chimpanzee, Gorilla, Human

**Applications:** IHC-P

(See our web site product page for detailed applications information)

**Protocols:** See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

**Specificity:** C-terminal cytoplasmic domain of human .

**Form:** Liquid

**Purification:** Immunoaffinity purification

**Recommend Usage:** Immunohistochemistry

(Formalin/PFA-fixed paraffin-embedded sections) (10 ug/mL)

The optimal working dilution should be determined by the end user.

**Storage Buffer:** In PBS (0.1% sodium azide)

**Storage Instruction:** Store at 4°C. For long term storage store at -80°C.

Aliquot to avoid repeated freezing and thawing.

**Entrez GeneID:** 2838

**Gene Symbol:** GPR15

**Gene Alias:** MGC126828, MGC126830