

## Datasheet

### TNNI3 monoclonal antibody, clone 2Q1100

**Catalog Number:** MAB8049

**Regulation Status:** For research use only (RUO)

**Product Description:** Mouse monoclonal antibody raised against TNNI3.

**Clone Name:** 2Q1100

**Immunogen:** Bovine TNNI3.

**Host:** Mouse

**Reactivity:** Bovine, Chicken, Frog, Human, Mouse, Rabbit

**Applications:** ELISA, IHC-P, WB

(See our web site product page for detailed applications information)

**Protocols:** See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

**Form:** Liquid

**Isotype:** IgG2b

**Recommend Usage:** Immunohistochemistry

(Formalin/PFA-fixed paraffin-embedded sections) (2.5-5 ug/mL)

The optimal working dilution should be determined by the end user.

**Storage Buffer:** In PBS, pH 7.4 (40% glycerol, 0.1% sodium azide)

**Storage Instruction:** Store at 4°C for three months. For long term storage store at -20°C.

Aliquot to avoid repeated freezing and thawing.

**Entrez GeneID:** 511094

**Gene Symbol:** TNNI3

**Gene Alias:** -