

Datasheet

ZNF650 polyclonal antibody (A01)

Catalog Number: H00130507-A01

Regulation Status: For research use only (RUO)

Product Description: Mouse polyclonal antibody raised against a partial recombinant ZNF650.

Immunogen: ZNF650 (NP_742067, 1 a.a. ~ 110 a.a)
partial recombinant protein with GST tag.

Sequence:

MNKRIIEICRKVTPPVPPKKVTAAEKKTLCKEERRQK
ARERQQKLLAEFASRQKSFMETAMDVDSPENDIPMEI
TTAEPQVSEAVYDCVICGQSGPSSDRPTGLVLL

Host: Mouse

Reactivity: Human

Applications: ELISA, WB-Re, WB-Ti

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Storage Buffer: 50 % glycerol

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 130507

Gene Symbol: UBR3

Gene Alias: DKFZp434P117, DKFZp686N10185,
FLJ37422, KIAA2024, MGC126489, ZNF650