

## Datasheet

### NCOA7 polyclonal antibody

**Gene Symbol:** NCOA7

**Catalog Number:** PAB22754

**Gene Alias:** ERAP140, ESNA1, FLJ45605, MGC88425, Nbla00052, Nbla10993, dJ187J11.3

**Regulation Status:** For research use only (RUO)

**Product Description:** Rabbit polyclonal antibody raised against recombinant NCOA7.

**Immunogen:** Recombinant protein corresponding to amino acids of human NCOA7.

**Sequence:**

EPLPVKLNSSSTEANVIKEALDSSLESTLDNSCQGAQMD  
NKSEVQLWLLKRIQVPIEDILPSKEEKSSTPPMFLCIKV  
GKPMRKSFATHAAMVQQYGKRR

**Host:** Rabbit

**Reactivity:** Human

**Applications:** IHC-P, WB

(See our web site product page for detailed applications information)

**Protocols:** See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

**Form:** Liquid

**Purification:** Antigen affinity purification

**Isotype:** IgG

**Recommend Usage:** Immunohistochemistry

(1:50-1:200)

Western Blot (1:250-1:500)

The optimal working dilution should be determined by the end user.

**Storage Buffer:** In PBS, pH 7.5 (40% glycerol, 0.02% sodium azide)

**Storage Instruction:** Store at 4°C. For long term storage store at -20°C.

Aliquot to avoid repeated freezing and thawing.

**Entrez GeneID:** 135112