

Datasheet

AFAP1L2 polyclonal antibody

Gene Symbol: AFAP1L2**Catalog Number:** PAB23174**Gene Alias:** FLJ14564, KIAA1914, XB130**Regulation Status:** For research use only (RUO)**Product Description:** Rabbit polyclonal antibody raised against recombinant AFAP1L2.**Immunogen:** Recombinant protein corresponding to amino acids of human AFAP1L2.**Sequence:**SPTLSCLDNATEALPADSGPGPTPDEPCIKCPENLGE
QQLESLEPEDPSLRITTVKIQTEQQRISFPPSCPDVVA
TPPGASPPVKD**Host:** Rabbit**Reactivity:** Human**Applications:** IF, IHC-P

(See our web site product page for detailed applications information)

Protocols: See our web site at<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols**Form:** Liquid**Purification:** Antigen affinity purification**Isotype:** IgG**Recommend Usage:** Immunohistochemistry

(1:200-1:500)

Immunofluorescence (1-4 ug/mL)

The optimal working dilution should be determined by the end user.

Storage Buffer: In PBS, pH 7.5 (40% glycerol, 0.02% sodium azide)**Storage Instruction:** Store at 4°C. For long term storage store at -20°C.

Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 84632