

## Datasheet

### MCF2L2 polyclonal antibody

**Gene Symbol:** MCF2L2**Catalog Number:** PAB23368**Gene Alias:** DKFZp686K0690, FLJ42509, KIAA0861**Regulation Status:** For research use only (RUO)**Product Description:** Rabbit polyclonal antibody raised against recombinant MCF2L2.**Immunogen:** Recombinant protein corresponding to amino acids of human MCF2L2.**Sequence:**PHPESSPKWVSSKTSQPSTSVPLARPLRTSEEPYTET  
ELNSRGKEDDETKFEVKSEEIFESHHERGNPELEQQA  
RLGDLSPRRRIIRD**Host:** Rabbit**Reactivity:** Human**Applications:** IHC-P

(See our web site product page for detailed applications information)

**Protocols:** See our web site at<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols**Form:** Liquid**Purification:** Antigen affinity purification**Isotype:** IgG**Recommend Usage:** Immunohistochemistry

(1:50-1:200)

Western Blot (1:250-1:500)

The optimal working dilution should be determined by the end user.

**Storage Buffer:** In PBS, pH 7.5 (40% glycerol, 0.02% sodium azide)**Storage Instruction:** Store at 4°C. For long term storage store at -20°C.

Aliquot to avoid repeated freezing and thawing.

**Entrez GeneID:** 23101