

Datasheet

IPO4 polyclonal antibody

Gene Alias: FLJ23338, Imp4, MGC131665**Catalog Number:** PAB23384**Regulation Status:** For research use only (RUO)**Product Description:** Rabbit polyclonal antibody raised against recombinant IPO4.**Immunogen:** Recombinant protein corresponding to amino acids of human IPO4.**Sequence:**AFLPYMESVFEEVFKLLECPHLNVRKAAHEALGQFCC
ALHKACQSCPSEPNTAALQAALARVVPSYMQAVNRE
RERQVVMVLE**Host:** Rabbit**Reactivity:** Human**Applications:** IHC-P

(See our web site product page for detailed applications information)

Protocols: See our web site at<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols**Form:** Liquid**Purification:** Antigen affinity purification**Isotype:** IgG**Recommend Usage:** Immunohistochemistry

(1:50-1:200)

The optimal working dilution should be determined by the end user.

Storage Buffer: In PBS, pH 7.5 (40% glycerol, 0.02% sodium azide)**Storage Instruction:** Store at 4°C. For long term storage store at -20°C.

Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 79711**Gene Symbol:** IPO4