

## Datasheet

### SLC10A7 polyclonal antibody

**Gene Alias:** C4orf13, DKFZp313H0531,  
DKFZp566M114, DKFZp779O2438, MGC25043, P7

**Catalog Number:** PAB23468

**Regulation Status:** For research use only (RUO)

**Product Description:** Rabbit polyclonal antibody raised against recombinant SLC10A7.

**Immunogen:** Recombinant protein corresponding to amino acids of human SLC10A7.

**Sequence:**

LSITPINEWLLKGLQTVGCMPPPVSSAVILTKAVGGNE  
AAAFNSAFGSFLVSKHSLTCLLQL

**Host:** Rabbit

**Reactivity:** Human

**Applications:** IHC-P

(See our web site product page for detailed applications information)

**Protocols:** See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

**Form:** Liquid

**Purification:** Antigen affinity purification

**Isotype:** IgG

**Recommend Usage:** Immunohistochemistry

(1:50-1:200)

The optimal working dilution should be determined by the end user.

**Storage Buffer:** In PBS, pH 7.5 (40% glycerol, 0.02% sodium azide)

**Storage Instruction:** Store at 4°C. For long term storage store at -20°C.  
Aliquot to avoid repeated freezing and thawing.

**Entrez GeneID:** 84068

**Gene Symbol:** SLC10A7