

Datasheet

HYLS1 polyclonal antibody

Catalog Number: PAB23770

Regulation Status: For research use only (RUO)

Product Description: Rabbit polyclonal antibody raised against recombinant HYLS1.

Immunogen: Recombinant protein corresponding to amino acids of human HYLS1.

Sequence:

MEELLPDGQIWANMDPEERMLAAATAFTHCAGQGEG
DVRREAQSIQYDPYSKASVAPGKRPALPVQLQYPHVE
SNVPSETVSEASQRLRKPVMK

Host: Rabbit

Reactivity: Human

Applications: IF, IHC-P

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Form: Liquid

Purification: Antigen affinity purification

Isotype: IgG

Recommend Usage: Immunohistochemistry

(1:500-1:1000)

Immunofluorescence (1-4 ug/mL)

The optimal working dilution should be determined by the end user.

Storage Buffer: In PBS, pH 7.5 (40% glycerol, 0.02% sodium azide)

Storage Instruction: Store at 4°C. For long term storage store at -20°C.

Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 219844

Gene Symbol: HYLS1

Gene Alias: FLJ32915, HLS

Gene Summary: This gene encodes a protein localized to the cytoplasm. Mutations in this gene are associated with hydroletharus syndrome. Multiple alternatively spliced variants, encoding the same protein, have been identified. [provided by RefSeq]