

Datasheet

D4S234E monoclonal antibody (M03), clone 1D22

Catalog Number: H00027065-M03

Regulation Status: For research use only (RUO)

Product Description: Mouse monoclonal antibody raised against a full-length recombinant D4S234E.

Clone Name: 1D22

Immunogen: D4S234E (AAH01745, 1 a.a. ~ 185 a.a)
full-length recombinant protein with GST tag. MW of the GST tag alone is 26 KDa.

Sequence:

MVKLGNNFAEKGTKQPLLEDGFDTIPLMTPLDVNQLQ
FPPDPKVVVKTKTEYEPDRKKGKARPPQIAEFTVSITE
GVTERFKVSVLVLFALAFLTCVVFLVVYKVYKYDRACP
DGFVLKNTQCIEGLESYAEQDSSAREKFYTVINHYN
LAKQSITRSVSPWMSVLSEEKLSEQETEAEEKSA

Host: Mouse

Reactivity: Human

Applications: ELISA, IF, S-ELISA, WB-Re
(See our web site product page for detailed applications information)

Protocols: See our web site at
<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Isotype: IgG2a Kappa

Storage Buffer: In 1x PBS, pH 7.4

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 27065

Gene Symbol: D4S234E

Gene Alias: D4S234, NEEP21, NSG1, P21