

Datasheet

ZNF37A monoclonal antibody (M03), clone 4H9

Catalog Number: H00007587-M03

Regulation Status: For research use only (RUO)

Product Description: Mouse monoclonal antibody
raised against a partial recombinant ZNF37A.

Clone Name: 4H9

Immunogen: ZNF37A (NP_001007095, 121 a.a. ~ 230
a.a) partial recombinant protein with GST tag. MW of the
GST tag alone is 26 KDa.

Sequence:

NKNGNSFWLNEDLIWHQKIKNWEQSFEYNECGKAFF
ENSLFLVHKRGYTGQKTCKYTEHKGKTCDSFFITHQQ
THPRENHYGNECGENIFEESILLEHQSVPFSQKLNL

Host: Mouse

Reactivity: Human

Applications: ELISA, S-ELISA, WB-Re
(See our web site product page for detailed applications
information)

Protocols: See our web site at
<http://www.abnova.com/support/protocols.asp> or product
page for detailed protocols

Isotype: IgG2a Lambda

Storage Buffer: In 1x PBS, pH 7.4

Storage Instruction: Store at -20°C or lower. Aliquot to
avoid repeated freezing and thawing.

Entrez GeneID: 7587

Gene Symbol: ZNF37A

Gene Alias: FLJ3472, KOX21, ZNF37