

Datasheet

NXNL2 polyclonal antibody

Gene Alias: C9orf121**Catalog Number:** PAB24420**Regulation Status:** For research use only (RUO)**Product Description:** Rabbit polyclonal antibody raised against recombinant NXNL2.**Immunogen:** Recombinant protein corresponding to amino acids of human NXNL2.**Sequence:**EMLDFMRELHGAWLALPFHDPYRHELRKRYNVTAI
PKLVIVKQNGEVITNKGRKQIRERGLACFQDWVEAADIFQ
N**Host:** Rabbit**Reactivity:** Human**Applications:** IHC-P

(See our web site product page for detailed applications information)

Protocols: See our web site at<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols**Form:** Liquid**Purification:** Antigen affinity purification**Isotype:** IgG**Recommend Usage:** Immunohistochemistry (1:20-1:50)

The optimal working dilution should be determined by the end user.

Storage Buffer: In PBS, pH 7.5 (40% glycerol, 0.02% sodium azide)**Storage Instruction:** Store at 4°C. For long term storage store at -20°C.
Aliquot to avoid repeated freezing and thawing.**Entrez GeneID:** 158046**Gene Symbol:** NXNL2