



Goat anti-Glutathione-S-Transferase (GST) conjugated to Dylight® 550

Product Number	D9-1310
Lot#	DY550011-13-001
Amount	100 µg
Concentration	1.39 mg/mL
Store at	2-8°C

Form/Shipping & Storage

Supplied as a liquid. Upon receipt, store at 2-8°C in the dark, do not freeze.

Handling

We recommend that the investigator determine the appropriate working concentration for their specific application.

Avoid exposure to heat and light.

Buffer

The product is in 100 mM sodium phosphate (pH 7.4), 100 mM sodium chloride, 2mM sodium azide as a preservative.

For research use only, not for diagnostic or therapeutic use.

Spectral Characteristics

Visible absorption maxima	557
Emission maximum	576
Dylight 550/α-GST Ratio	5.16