

## Product Specifications

	<b>VWR Part Number:</b>	<b>IR1434</b>
	<b>ImmunoReagents, Inc. Part Number:</b>	GtxDk-003-D
<b>Product:</b>	GOAT X DONKEY IGG AP 1VL	
<b>Concentration:</b>	> 4.5 mg/ml (E 1% at 280 nm = 13.0)	
<b>Amount:</b>	2.0 mg	
<b>Conjugate:</b>	Unconjugated	
<b>Form:</b>	Clear, colorless liquid, 0.2 µm filtered	
<b>Purification:</b>	Affinity purified using solid phase Donkey IgG	
<b>Purity:</b>	> 95% based on SDS-PAGE	
<b>Host:</b>	Goat	
<b>Immunogen:</b>	Purified Donkey IgG, whole molecule	
<b>Buffer:</b>	10 mM Sodium Phosphate, 0.15 M Sodium Chloride, pH 7.2	
<b>Storage:</b>	2-8 °C	
<b>Shelf Life:</b>	1 year from date of receipt. Prepare working dilution prior to use and then discard.	
<b>Specificity:</b>	Based on IEP, this antibody reacts with: · heavy (?) chains on donkey IgG · light chains on all donkey immunoglobulins	
<b>Cross Reactivity:</b>	Based on IEP, no reactivity is observed to: · non-immunoglobulin donkey serum immunoglobulins	
<b>Country of Origin:</b>	Goat serum was obtained from healthy animals of US origin and under the care of a registered veterinarian.	
<b>Applications:</b>	This antibody is suitable for all immunoassay applications. The optimal working dilution should be determined by the investigator.	
<b>Disclaimer:</b>	For in vitro Laboratory Use Only. Not for diagnostic or therapeutic use. Not for human or animal consumption. Suggested applications of our products are not recommendations to use our products in violation of any patent or as a license under any patent of ImmunoReagents, Inc.	

Product may not be resold or modified for resale without prior written approval of ImmunoReagents, Inc.