

## Product Specifications

	<b>VWR Part Number:</b>	<b>IR2388</b>
	<b>ImmunoReagents, Inc. Part Number:</b>	<b>Ha-003-Z</b>
<b>Product:</b>	IGGPROTEIN GHAMSTER10MG	
<b>Concentration:</b>	> 4.5 mg/ml (E 1% at 280 nm = 13.0)	
<b>Amount:</b>	10 mg	
<b>Conjugate:</b>	Unconjugated	
<b>Form:</b>	Clear, colorless liquid, 0.2 µm filtered	
<b>Purification:</b>	Protein G	
<b>Purity:</b>	> 95% based on SDS-PAGE	
<b>Host:</b>	Hamster	
<b>Immunogen:</b>	N/A	
<b>Buffer:</b>	10 mM Sodium Phosphate, 0.15 M Sodium Chloride, pH 7.2	
<b>Storage:</b>	2-8 °C	
<b>Shelf Life:</b>	1 year from date of receipt. Prepare working dilution prior to use and then discard.	
<b>Specificity:</b>	N/A	
<b>Cross Reactivity:</b>	N/A	
<b>Country of Origin:</b>	Normal Hamster Serum was obtained from China.	
<b>Applications:</b>	For use as a standard or control in most immunoassay formats.	
<b>Disclaimer:</b>	For in vitro Laboratory Use Only. Not for diagnostic or therapeutic use. Not for human or animal consumption. Suggested applications of our products are not recommendations to use our products in violation of any patent or as a license under any patent of ImmunoReagents, Inc.	

Product may not be resold or modified for resale without prior written approval of ImmunoReagents, Inc.