

## Product Specifications

	<b>VWR Part Number:</b>	<b>IR2744</b>
	<b>ImmunoReagents, Inc. Part Number:</b>	<b>PAR-100-IL6</b>
<b>Product:</b>	RABBIT ANTI-IL-6	
<b>Concentration:</b>	N/A	
<b>Amount:</b>	100 µg	
<b>Conjugate:</b>	Unconjugated	
<b>Form:</b>	Lyophilized	
<b>Purification:</b>	Protein A	
<b>Purity:</b>	> 90% based on SDS-PAGE	
<b>Host:</b>	Rabbit	
<b>Immunogen:</b>	Human IL-6	
<b>Buffer:</b>	0.02 M Potassium Phosphate, 0.15 M Sodium Chloride, pH 7.2 with no stabilizers or preservatives	
<b>Storage:</b>	Store at 2-8°C after restoration with 0.1mL deionized water or -20°C for long term storage, avoid repeat freeze thaws.	
<b>Shelf Life:</b>	1 year from date of receipt. Prepare working dilution prior to use and then discard.	
<b>Specificity:</b>	Human IL-6	
<b>Cross Reactivity:</b>	N/A	
<b>Country of Origin:</b>	US Origin	
<b>Applications:</b>	Western blot analysis of recombinant human IL-7 (100-11) using rabbit anti-human IL-7 polyclonal antibody and anti-rabbit secondary antibodies. MW of human IL-7 is 17.5 kDa.	
<b>Disclaimer:</b>	For in vitro Laboratory Use Only. Not for diagnostic or therapeutic use. Not for human or animal consumption. Suggested applications of our products are not recommendations to use our products in violation of any patent or as a license under any patent of ImmunoReagents, Inc.	

Product may not be resold or modified for resale without prior written approval of ImmunoReagents, Inc.