

---

---

## Product Specifications

	<b>VWR Part Number:</b>	<b>IR2758</b>
	<b>ImmunoReagents, Inc. Part Number:</b>	<b>PAR-200-GMCSF</b>
<b>Product:</b>	RABBIT ANTI-GM-CSF	
<b>Concentration:</b>	N/A	
<b>Amount:</b>	100 µg	
<b>Conjugate:</b>	Unconjugated	
<b>Form:</b>	Lyophilized	
<b>Purification:</b>	Protein A	
<b>Purity:</b>	> 90% based on SDS-PAGE	
<b>Host:</b>	Rabbit	
<b>Immunogen:</b>	Mouse GM-CSF	
<b>Buffer:</b>	0.02 M Potassium Phosphate, 0.15 M Sodium Chloride, pH 7.2 with no stabilizers or preservatives	
<b>Storage:</b>	Store at 2-8°C after restoration with 0.1mL deionized water or -20°C for long term storage, avoid repeat freeze thaws.	
<b>Shelf Life:</b>	1 year from date of receipt. Prepare working dilution prior to use and then discard.	
<b>Specificity:</b>	Mouse GM-CSF	
<b>Cross Reactivity:</b>	Polyclonal anti-mouse GM-SCF shows slight cross-reactivity with recombinant human GM-CSF (shown in figure below).	
<b>Country of Origin:</b>	US Origin	
<b>Applications:</b>	For use as a standard or control in most immunoassay formats.	
<b>Disclaimer:</b>	For in vitro Laboratory Use Only. Not for diagnostic or therapeutic use. Not for human or animal consumption. Suggested applications of our products are not recommendations to use our products in violation of any patent or as a license under any patent of ImmunoReagents, Inc.	

Product may not be resold or modified for resale without prior written approval of ImmunoReagents, Inc.