



Orexin B Antibody

CATALOG NUMBER: 54-204

Specifications

SPECIES REACTIVITY:	Human, Mouse
TESTED APPLICATIONS:	ELISA
APPLICATIONS:	Orexin B antibody can be used at 1:2000-1:5000 as detecting antibodies and 1:200-1:1000 as coating antibodies in sandwich ELISA.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	Orexin B antibody reacts with Orexin B of human, mouse, rat and many other mammalian species.
IMMUNOGEN:	Human Orexin B peptide aa1-14
HOST SPECIES:	Chicken

Properties

PURIFICATION:	Affinity Purified
PHYSICAL STATE:	Liquid
BUFFER:	PBS Buffer containing 0.02% sodium azide.
STORAGE CONDITIONS:	2-8°C for one week and -20°C as an undiluted liquid for up to two years.
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	OX, PPORX, PPOX, Orexin, Hypocretin, Hcrt, NRCLP1
ACCESSION NO.:	NP_001515.1
PROTEIN GI NO.:	4557635
OFFICIAL SYMBOL:	HCRT
GENE ID:	3060

Background

FOR RESEARCH USE ONLY

December 13, 2016