



RbAp48 Antibody [3-255]

CATALOG NUMBER: 47-102

Specifications

| | |
|-----------------------------|---|
| SPECIES REACTIVITY: | Human |
| TESTED APPLICATIONS: | IF, IP, WB |
| USER NOTE: | Optimal dilutions for each application to be determined by the researcher. |
| POSITIVE CONTROL: | 1) Cat. No. 1205 - MOLT4 Cell Lysate 2) Cat. No. 1201 - HeLa Cell Lysate |
| IMMUNOGEN: | GST fusion protein containing the complete coding region (aa 1-425) of RbAp48 expressed in E. coli. |
| HOST SPECIES: | Mouse |

Properties

| | |
|----------------------------|--|
| PURIFICATION: | Protein G-purified |
| PHYSICAL STATE: | Liquid |
| STORAGE CONDITIONS: | RbAp48 monoclonal antibody can be stored at 4°C, stable for one year. As with all antibodies care should be taken to avoid repeated freeze thaw cycles. Antibodies should not be exposed to prolonged high temperatures. |
| CLONALITY: | Monoclonal |
| ISOTYPE: | IgG2a/kappa |
| CONJUGATE: | Unconjugated |

Additional Info

| | |
|-------------------------|---|
| ALTERNATE NAMES: | RBAP48, Histone-binding protein RBBP4, Chromatin assembly factor 1 subunit C, CAF-1 subunit C, NURF55 |
| ACCESSION NO.: | Q09028 |
| PROTEIN GI NO.: | 1172846 |
| OFFICIAL SYMBOL: | RBBP4 |
| GENE ID: | 5928 |

Background

FOR RESEARCH USE ONLY

December 13, 2016