



BRCA1 Antibody [3A2]

CATALOG NUMBER: 47-113

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	IP, WB
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
POSITIVE CONTROL:	1) Cat. No. 1369 - Human Lymph Node Tissue Lysate
IMMUNOGEN:	GST fusion protein expressed in E. coli corresponding to aa 762-1315 of full-length BRCA1.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein G-purified
PHYSICAL STATE:	Liquid
BUFFER:	PBS
STORAGE CONDITIONS:	BRCA1 monoclonal antibody can be stored at 4°C, stable for one year. As with all antibodies care should be taken to avoid repeated freeze thaw cycles. Antibodies should not be exposed to prolonged high temperatures.
CLONALITY:	Monoclonal
ISOTYPE:	IgG1/kappa
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	Serine-protein kinase ATM, Ataxia telangiectasia mutated, A-T mutated, AT1, ATA, ATC, ATD, ATE, ATDC, TEL1, TELO1
ACCESSION NO.:	NP_000042.3
PROTEIN GI NO.:	71902540
OFFICIAL SYMBOL:	ATM
GENE ID:	472

Background

FOR RESEARCH USE ONLY

December 13, 2016