



AIB1 Antibody [AC3]

CATALOG NUMBER: 47-118

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	WB
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
POSITIVE CONTROL:	1) Cat. No. 1219 - MCF7 Cell Lysate
IMMUNOGEN:	Peptide corresponding to the C-terminus of human AIB1 conjugated to keyhole limpet hemocyanin (KLH).
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein G-purified
PHYSICAL STATE:	Liquid
BUFFER:	PBS containing 0.01% sodium azide.
STORAGE CONDITIONS:	AIB1 monoclonal antibody can be stored at 4°C, stable for one year. As with all antibodies care should be taken to avoid repeated freeze thaw cycles. Antibodies should not be exposed to prolonged high temperatures.
CLONALITY:	Monoclonal
ISOTYPE:	IgG1/kappa
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	RBBP3, Transcription factor E2F1, PBR3, E2F-1, RBP3, RBAP1
ACCESSION NO.:	NP_005216.1
PROTEIN GI NO.:	400928
OFFICIAL SYMBOL:	E2F1
GENE ID:	1869

Background

FOR RESEARCH USE ONLY

December 13, 2016