



## KLK4 Antibody

CATALOG NUMBER: 47-163

### Specifications

<b>SPECIES REACTIVITY:</b>	Human
<b>TESTED APPLICATIONS:</b>	WB
<b>USER NOTE:</b>	Optimal dilutions for each application to be determined by the researcher.
<b>IMMUNOGEN:</b>	Peptide corresponding to aa 242-254 of human KLK4 protein.
<b>HOST SPECIES:</b>	Rabbit

### Properties

<b>PURIFICATION:</b>	Affinity-purified
<b>PHYSICAL STATE:</b>	Liquid
<b>BUFFER:</b>	PBS containing 0.02% sodium azide.
<b>STORAGE CONDITIONS:</b>	KLK4 antibody can be stored at 4°C, stable for one year. As with all antibodies care should be taken to avoid repeated freeze thaw cycles. Antibodies should not be exposed to prolonged high temperatures.
<b>CLONALITY:</b>	Polyclonal
<b>CONJUGATE:</b>	Unconjugated

### Additional Info

<b>ALTERNATE NAMES:</b>	Kallikrein-15, ACO protease, ACO, HSRNASPH
<b>ACCESSION NO.:</b>	Q9H2R5
<b>PROTEIN GI NO.:</b>	18202940
<b>OFFICIAL SYMBOL:</b>	KLK15
<b>GENE ID:</b>	55554

### Background

FOR RESEARCH USE ONLY

December 13, 2016