



KLK5 Antibody

CATALOG NUMBER: 47-164

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	WB
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Peptide corresponding to aa 280-293 of human KLK5 protein.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Affinity-purified
PHYSICAL STATE:	Liquid
BUFFER:	PBS containing 0.02% sodium azide.
STORAGE CONDITIONS:	KLK5 antibody can be stored at 4°C, stable for one year. As with all antibodies care should be taken to avoid repeated freeze thaw cycles. Antibodies should not be exposed to prolonged high temperatures.
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	Transcription regulator protein BACH1, BTB and CNC homolog 1, BACH-1
ACCESSION NO.:	O14867
PROTEIN GI NO.:	6686266
OFFICIAL SYMBOL:	BACH1
GENE ID:	571

Background

FOR RESEARCH USE ONLY

December 13, 2016