



KLK9 Antibody

CATALOG NUMBER: 47-165

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	WB
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Peptide corresponding to aa 239-250 of human KLK9 protein.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Affinity-purified
PHYSICAL STATE:	Liquid
BUFFER:	PBS containing 0.02% sodium azide.
STORAGE CONDITIONS:	KLK9 antibody can be stored at 4°C, stable for one year. As with all antibodies care should be taken to avoid repeated freeze thaw cycles. Antibodies should not be exposed to prolonged high temperatures.
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	HCNP, KIAA1177, SYF1, PP3898, Pre-mRNA-splicing factor SYF1, Protein HCNP, HCRN, NTC90
ACCESSION NO.:	Q9HCS7
PROTEIN GI NO.:	25091548
OFFICIAL SYMBOL:	XAB2
GENE ID:	56949

Background

FOR RESEARCH USE ONLY

December 13, 2016