



## KLK12 Antibody

CATALOG NUMBER: 47-166

### Specifications

<b>SPECIES REACTIVITY:</b>	Human
<b>TESTED APPLICATIONS:</b>	WB
<b>USER NOTE:</b>	Optimal dilutions for each application to be determined by the researcher.
<b>IMMUNOGEN:</b>	Peptide corresponding to aa 236-248 of human KLK12 protein.
<b>HOST SPECIES:</b>	Rabbit

### Properties

<b>PURIFICATION:</b>	Affinity-purified
<b>PHYSICAL STATE:</b>	Liquid
<b>BUFFER:</b>	PBS containing 0.02% sodium azide.
<b>STORAGE CONDITIONS:</b>	KLK12 antibody can be stored at 4°C, stable for one year. As with all antibodies care should be taken to avoid repeated freeze thaw cycles. Antibodies should not be exposed to prolonged high temperatures.
<b>CLONALITY:</b>	Polyclonal
<b>CONJUGATE:</b>	Unconjugated

### Additional Info

<b>ALTERNATE NAMES:</b>	ERT, ESX, JEN, ETS-related transcription factor Elf-3, E74-like factor 3, ESE-1, EPR-1
<b>ACCESSION NO.:</b>	P78545
<b>PROTEIN GI NO.:</b>	74739735
<b>OFFICIAL SYMBOL:</b>	ELF3
<b>GENE ID:</b>	1999

### Background

FOR RESEARCH USE ONLY

December 13, 2016