



KLK14 Antibody

CATALOG NUMBER: 47-168

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	WB
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Peptide corresponding to aa 239-251 of human KLK14 protein.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Affinity-purified
PHYSICAL STATE:	Liquid
BUFFER:	PBS containing 0.02% sodium azide.
STORAGE CONDITIONS:	KLK14 antibody can be stored at 4°C, stable for one year. As with all antibodies care should be taken to avoid repeated freeze thaw cycles. Antibodies should not be exposed to prolonged high temperatures.
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	Retinoblastoma, phospho-Retinoblastoma, phospho-Rb, pT826, Retinoblastoma-associated protein, p105-Rb, Rb, RB, pRb, OSRC, pp110
ACCESSION NO.:	AAO62758.1
PROTEIN GI NO.:	29123599
OFFICIAL SYMBOL:	RB1
GENE ID:	5925

Background

FOR RESEARCH USE ONLY

December 13, 2016