



RAD17 Antibody

CATALOG NUMBER: 47-157

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	WB
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Peptide corresponding to aa 2-15 of human RAD17.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Immunoaffinity chroma-tography
PHYSICAL STATE:	Liquid
BUFFER:	PBS containing 0.02% sodium azide.
STORAGE CONDITIONS:	RAD17 antibody can be stored at 4°C, stable for one year. As with all antibodies care should be taken to avoid repeated freeze thaw cycles. Antibodies should not be exposed to prolonged high temperatures.
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	SCTE, UNQ570/PRO1132, Kallikrein-5, Kallikrein-like protein 2, KLK-L2, KLKL2
ACCESSION NO.:	Q9Y337
PROTEIN GI NO.:	296434569
OFFICIAL SYMBOL:	KLK5
GENE ID:	25818

Background

FOR RESEARCH USE ONLY

December 13, 2016