



RTKN2 Antibody [2C2]

CATALOG NUMBER: 70-108

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	RTKN2 Monoclonal Antibody can be used for immunohistochemistry (tested on parafin embedded tissues) starting at 1:50 and Western Blot starting at 1:500 - 1:100.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	E.coli derived recombinant Human MIP-3alpha.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.2
STORAGE CONDITIONS:	RTKN2 Monoclonal antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG2a,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	RTKN2, BA531F24.1, Em:AC024597.2, Rhotekin-2, PLEKHK1, Rhotekin 2
ACCESSION NO.:	Q8IZC4
PROTEIN GI NO.:	74750788
OFFICIAL SYMBOL:	RTKN2
GENE ID:	219790

Background

FOR RESEARCH USE ONLY

December 13, 2016