



TARBP2 Antibody [1D9]

CATALOG NUMBER: 70-141

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC, IP, WB
APPLICATIONS:	TARBP2 Monoclonal Antibody can be used for immunohistochemistry (tested on parafin embedded tissues) starting at 5 ug/mL and Western Blot starting at 1:500 - 1:1000.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Recombinant protein
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.2
CONCENTRATION:	0.47 mg/ml
STORAGE CONDITIONS:	TARBP2 Monoclonal antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG2a,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	TARBP2, TAR RNA binding protein 2, TRBP1, TRBP2, TAR RNA-binding protein 2, TRBP, LOQS
ACCESSION NO.:	Q15633
PROTEIN GI NO.:	209572714
OFFICIAL SYMBOL:	TARBP2
GENE ID:	6895

Background

FOR RESEARCH USE ONLY

December 13, 2016