



CAMK1D Antibody [3H8]

CATALOG NUMBER: 70-190

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	CAMK1D Monoclonal Antibody can be used for immunohistochemistry (tested on paraffin embedded tissues) starting at 5 ug/mL and Western Blot starting at 1:500 - 1:1000.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	CAMK1D (AAH35745, 1 a.a. ~ 96 a.a) partial recombinant protein with GST tag. MW of the GST tag alone is 26 KDa.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.2
STORAGE CONDITIONS:	CAMK1D Monoclonal antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG2b,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	CAMK1D, CaM kinase ID, CaMKI-like protein kinase, CaMKID, CKLiK, CaM kinase I delta, CaM-K1, CaMKI delta, CaM-KI delta, CaMKI-like kinase
ACCESSION NO.:	Q8IU85
PROTEIN GI NO.:	56404610
OFFICIAL SYMBOL:	CAMK1D
GENE ID:	57118

Background

FOR RESEARCH USE ONLY

December 13, 2016