



KRT18 Antibody [DC-10]

CATALOG NUMBER: 70-200

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	FACS, IF, IHC
APPLICATIONS:	FACS, IF, IHC-P (1:50)
USER NOTE:	Product is photosensitive and should be protected from light.
SPECIFICITY:	The antibody DC-10 reacts with Cytokeratin 18 (45 kD) . Cytokeratins are a member of intermediate filaments subfamily represented in epithelial tissues.
IMMUNOGEN:	CAMK1D (AAH35745, 1 a.a. ~ 96 a.a) partial recombinant protein with GST tag. MW of the GST tag alone is 26 KDa.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	15 mM sodium azide, 0.2% BSA, PBS
STORAGE CONDITIONS:	KRT18 Monoclonal antibody may be stored at Store at +4°C. Do not freeze.
CLONALITY:	Monoclonal
ISOTYPE:	IgG1
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	KRT18, CK-18, Cytokeratin 18, Cytokeratin-18, K18, Keratin 18, CYK18, Keratin-18
ACCESSION NO.:	P05783
PROTEIN GI NO.:	125083
OFFICIAL SYMBOL:	KRT18
GENE ID:	3875

Background

FOR RESEARCH USE ONLY

December 13, 2016