



ADRM1 Antibody [3D11]

CATALOG NUMBER: 70-258

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	ADRM1 Monoclonal Antibody can be used for immunohistochemistry (tested on parafin embedded tissues) starting at 10 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Human Actin, Smooth Muscle.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.2
STORAGE CONDITIONS:	ADRM1 Monoclonal antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG2b,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	ADRM1, Adhesion regulating molecule 1, Adhesion-regulating molecule 1, ARM1, gp110, HRpn13, Rpn13 homolog, M(r) 110,000 surface antigen, ARM-1, Rpn13
ACCESSION NO.:	Q16186
PROTEIN GI NO.:	20141265
OFFICIAL SYMBOL:	ADRM1
GENE ID:	11047

Background

FOR RESEARCH USE ONLY

December 13, 2016