



AHSA1 Antibody [25F2.D10]

CATALOG NUMBER: 70-277

Specifications

SPECIES REACTIVITY:	Human, Mouse, Rat
TESTED APPLICATIONS:	ELISA, ICC, IF, IHC, IP, WB
APPLICATIONS:	AHSA1 antibody can be used for staining paraffin embedded tissues starting at 5 ug/mL, and Western Blot starting at 1 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	Detects ~38kD protein. Can run at up to 45kD on SDS-PAGE.
IMMUNOGEN:	Mouse Aha1.
HOST SPECIES:	Rat

Properties

PURIFICATION:	Protein G Column
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG2a,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	AHSA1, AHA1, C14orf3, p38
ACCESSION NO.:	O95433
PROTEIN GI NO.:	13124003
OFFICIAL SYMBOL:	AHSA1
GENE ID:	10598

Background

FOR RESEARCH USE ONLY

December 13, 2016