



DBH Antibody

CATALOG NUMBER: 70-281

Specifications

SPECIES REACTIVITY:	Human, Mouse, Primate
TESTED APPLICATIONS:	IHC, WB
APPLICATIONS:	DBH antibody can be used for staining paraffin embedded tissues starting at 1:100, Western Blot starting at 1:1000.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	Specific for the ~75k DBH protein in Western blots
IMMUNOGEN:	Peptide from the C-terminal region of human dopamine R-hydroxylase (DBH), conjugated to keyhole limpet hemocyanin (KLH).
HOST SPECIES:	Sheep

Properties

PURIFICATION:	Immunoaffinity Chromatography
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	DBH, Dopamine beta-monooxygenase, DBM, Dopamine beta-hydroxylase
ACCESSION NO.:	P09172
PROTEIN GI NO.:	158517849
OFFICIAL SYMBOL:	DBH
GENE ID:	1621

Background

FOR RESEARCH USE ONLY

December 13, 2016