



TUBB2B Antibody [AT5B3]

CATALOG NUMBER: 70-288

Specifications

| | |
|-----------------------------|---|
| SPECIES REACTIVITY: | Human |
| TESTED APPLICATIONS: | IHC |
| APPLICATIONS: | TUBB2B antibody can be used for staining paraffin embedded tissues starting at 5 ug/mL. |
| USER NOTE: | Optimal dilutions for each application to be determined by the researcher. |
| HOST SPECIES: | Mouse |

Properties

| | |
|----------------------------|---|
| PURIFICATION: | Protein G Column |
| CONCENTRATION: | 1 mg/ml |
| STORAGE CONDITIONS: | Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles. |
| CLONALITY: | Monoclonal |
| ISOTYPE: | IgG2a,k |
| CONJUGATE: | Unconjugated |

Additional Info

| | |
|-------------------------|---|
| ALTERNATE NAMES: | TUBB2B, BA506K6.1, Class IIb beta-tubulin, PMGYSA, RP11-506K6.1, Tubulin, beta 2B, Class II beta-tubulin isotype, Tubulin beta-2B chain, Tubulin, beta 2B class IIb |
| ACCESSION NO.: | Q9BVA1 |
| PROTEIN GI NO.: | 74761283 |
| OFFICIAL SYMBOL: | TUBB2B |
| GENE ID: | 347733 |

Background

FOR RESEARCH USE ONLY

December 13, 2016