



## EPCAM Antibody [Ber-EP4]

CATALOG NUMBER: 70-297

### Specifications

<b>SPECIES REACTIVITY:</b>	Human
<b>TESTED APPLICATIONS:</b>	IHC
<b>APPLICATIONS:</b>	EPCAM antibody can be used for staining paraffin embedded tissues starting at 1:50.
<b>USER NOTE:</b>	Optimal dilutions for each application to be determined by the researcher.
<b>IMMUNOGEN:</b>	MCF-7 human breast carcinoma cell line.
<b>HOST SPECIES:</b>	Mouse

### Properties

<b>STORAGE CONDITIONS:</b>	Antibody is stable for 24 months when stored at 2-8°C.
<b>CLONALITY:</b>	Monoclonal
<b>ISOTYPE:</b>	IgG1,k
<b>CONJUGATE:</b>	Unconjugated

### Additional Info

<b>ALTERNATE NAMES:</b>	EPCAM, 323/A3, ACSTD1, 17-1A, CD326, EGP, EGP34, Epithelial glycoprotein, GA733-2, HNPCC8, Ep-CAM, ESA, HEGP314, KS 1/4 antigen, KS1/4, KSA, M1S2, MIC18, MK-1, MH99, TROP1, TACST-1, TACSTD1, CD326 antigen, CO-17A, DIAR5, EGP-2, EGP314, EGP40, Epithelial glycoprotein 314, HEA125, Ly74, M4S1, MOC31
<b>ACCESSION NO.:</b>	P16422
<b>PROTEIN GI NO.:</b>	160266056
<b>OFFICIAL SYMBOL:</b>	EPCAM
<b>GENE ID:</b>	4072

### Background

FOR RESEARCH USE ONLY

December 13, 2016