



ADK Antibody [AT4F8]

CATALOG NUMBER: 70-303

Specifications

| | |
|-----------------------------|---|
| SPECIES REACTIVITY: | Human |
| TESTED APPLICATIONS: | ELISA, IHC, WB |
| APPLICATIONS: | ADK antibody can be used for staining paraffin embedded tissues starting at 5 ug/mL, and Western Blot starting at 1:1000. |
| USER NOTE: | Optimal dilutions for each application to be determined by the researcher. |
| SPECIFICITY: | Human ADK |
| IMMUNOGEN: | Recombinant protein |
| HOST SPECIES: | Mouse |

Properties

| | |
|----------------------------|---|
| PURIFICATION: | Protein G Column |
| STORAGE CONDITIONS: | Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles. |
| CLONALITY: | Monoclonal |
| ISOTYPE: | IgG1,k |
| CONJUGATE: | Unconjugated |

Additional Info

| | |
|-------------------------|---|
| ALTERNATE NAMES: | ADK, Adenosine 5-phosphotransferase, Adenosine kinase, AK |
| ACCESSION NO.: | P55263 |
| PROTEIN GI NO.: | 6840802 |
| OFFICIAL SYMBOL: | ADK |
| GENE ID: | 132 |

Background

FOR RESEARCH USE ONLY

December 13, 2016