



## AICDA Antibody

CATALOG NUMBER: 70-536

### Specifications

<b>SPECIES REACTIVITY:</b>	Human
<b>TESTED APPLICATIONS:</b>	IHC, WB
<b>APPLICATIONS:</b>	AICDA Antibody can be used for Immunohistochemistry in paraffin embeded tissues starting at 10 ug/mL, and Western Blotting starting at 1:500 - 1:2000.
<b>USER NOTE:</b>	Optimal dilutions for each application to be determined by the researcher.
<b>IMMUNOGEN:</b>	Synthetic peptide
<b>HOST SPECIES:</b>	Rabbit

### Properties

<b>PURIFICATION:</b>	Antiserum
<b>STORAGE CONDITIONS:</b>	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
<b>CLONALITY:</b>	Polyclonal
<b>CONJUGATE:</b>	Unconjugated

### Additional Info

<b>ALTERNATE NAMES:</b>	AICDA, AID, ARP2, CDA2, Cytidine aminohydrolase, HIGM2
<b>ACCESSION NO.:</b>	Q9GZX7
<b>PROTEIN GI NO.:</b>	23813666
<b>OFFICIAL SYMBOL:</b>	AICDA
<b>GENE ID:</b>	57379

### Background

FOR RESEARCH USE ONLY

December 13, 2016